



Unmanaged Plug-and-Play Ethernet Switches  
for Assembly on DIN Rail in Control Cabinets

Commercial Temp.: 0 °C ... +55 °C / Industrial Temp.: -40 °C ... +70 °C

## Specification

Number of ports copper / termination	8 x 10BASE-Te / 100BASE-TX EEE / RJ45 (twisted pair)
Number of ports F.O. / termination	2 x 100BASE-FX / SC duplex socket
Nominal voltage	24 / 48 VDC =
Permissible voltage range	9 V ... 60 VDC =
Termination	Screw type terminal block, pluggable, 3-poles (+ / - / =)
Current consumption typical @ 24 V	See eCatalogue
Dimensions (W x H x D)	25.0 x 142.0 x 107.5 mm (without pluggable screw type terminal block)
Weight	531 g
MTBF	See eCatalogue
Approvals	CE
Approvals (in preparation)	Federal Communications Commission (FCC), cUL US 508 listed, Det Norske Veritas (DNV), Germanischer Lloyd (GL), American Bureau of Shipping (ABS), Nippon Kaiji Kyokai (NK)

Identification	Part number	Drawings	Dimensions in mm
Ha-VIS eCon 3082B-AD 0 °C ... +55 °C 2 x MM (2 km)	24 03 008 2110		
Ha-VIS eCon 3082B-AF 0 °C ... +55 °C 2 x SM (15 km)	24 03 008 2210		
Ha-VIS eCon 3082BT-AD -40 °C ... +70 °C 2 x MM (2 km)	24 03 008 2100		
Ha-VIS eCon 3082BT-AF -40 °C ... +70 °C 2 x SM (15 km)	24 03 008 2200		