


Number of contacts


48, 32




Female connectors

Identification	No. of contacts	Contact arrangement	Part number	Performance levels according to IEC 60 603-2. Explanation chapter 00		
				3	2	1
Female connector ¹⁾ "low profile" with solder pins 3.7 mm	48		09 06 248 7833	09 06 248 6833 09 06 248 6833 222 ^{f)}	09 06 248 2833 09 06 248 2833 222 ^{f)}	
	32					
	32					
Female connector ¹⁾ "low profile" with solder pins 4.5 mm	48		09 06 248 7833	09 06 248 6834 09 06 248 6834 222 ^{f)}	09 06 248 2834	
	32					
	32					
Female connector ¹⁾ "low profile" with press-in pins 4.5 mm	48		09 06 248 7832	09 06 248 6832	09 06 248 2832 09 06 248 2832 222 ^{f)}	
	32					
	32					
Female connector "low profile" with press-in pins 13 mm	48		09 06 248 7832	09 06 248 6832 09 06 248 6838*	09 06 248 2832 09 06 232 2832	
	32					

Dimensions



Board drillings
Mounting side



Dimensions in mm

* Wrap posts for interfacing selectively gold plated (performance level 2)

¹⁾ With shroud coding, see also chapter 00

^{f)} Railway classification NFF 16-101, Smoke index: F1, Flammability class: I2

^{w)} Wrap posts not for interfacing, no performance level