

Unmanaged Plug-and-Play Ethernet Switches
 for Assembly on DIN Rail in Control Cabinets
 Commercial Temp.: 0 °C ... +55 °C / Industrial Temp.: -40 °C ... +70 °C
 Power Sourcing Equipment (PSE) with 4 Ports PoE+ (34.2 watts per port)
 Integrated 24 / 54 V DC Voltage Transformer



Specification

Number of ports copper / termination including PoE+ ports	6 x 10BASE-Te / 100BASE-TX EEE / 1000BASE-T EEE RJ45 (twisted pair) 4 x PoE+ with 34.2 watts per port
Nominal voltage	24 / 48 VDC =
Permissible voltage range	18 V ... 60 VDC =
Termination	Screw type terminal block, pluggable, 3-poles (+ / - / =)
Current consumption typical @ 24 V	See eCatalogue
Dimensions (W x H x D)	60.0 x 142.0 x 107.5 mm (without pluggable screw type terminal block)
Weight	See eCatalogue
MTBF	See eCatalogue
Approvals	CE
Approvals (in preparation)	Federal Communications Commission (FCC), cUL US 508 listed Det Norske Veritas (DNV), Germanischer Lloyd (GL), American Bureau of Shipping (ABS), Nippon Kaiji Kyokai (NK)

Identification	Part number	Drawings	Dimensions in mm
Ha-VIS eCon 3060GB-A-PP 0 °C ... +55 °C	24 03 506 0030		
Ha-VIS eCon 3060GBT-A-PP -40 °C ... +70 °C	24 03 506 0020		