









Number of contacts

3

40 A 830 V 8 kV 3
 10 A 830 V 8 kV 3
 + 4 additional signal contacts

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)																												
		Male	Female																													
Han-Modular®, Han® CD module, Crimp termination  <p>Please order crimp contacts separately.</p>	0.14 ... 6	09 14 007 3001	09 14 007 3101	 <p>Contact arrangement (view from termination side)</p>																												
Han® C HMC, Crimp contact, Contact surface: HMC gold plated 	1.5 2.5 4 6 10	09 32 200 6114 09 32 200 6115 09 32 200 6119 09 32 200 6118 09 32 200 6117	09 32 200 6224 09 32 200 6225 09 32 200 6229 09 32 200 6228 09 32 200 6227	 <table border="1"> <thead> <tr> <th>Wire gauge</th> <th></th> <th>ø</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>1.5 mm²</td> <td>AWG 16</td> <td>1.75 mm</td> <td>9.5 mm</td> </tr> <tr> <td>2.5 mm²</td> <td>AWG 14</td> <td>2.25 mm</td> <td>9.5 mm</td> </tr> <tr> <td>4 mm²</td> <td>AWG 12</td> <td>2.85 mm</td> <td>9.5 mm</td> </tr> <tr> <td>6 mm²</td> <td>AWG 10</td> <td>3.5 mm</td> <td>9.5 mm</td> </tr> <tr> <td>10 mm²</td> <td>AWG 8</td> <td>4.3 mm</td> <td>15 mm</td> </tr> </tbody> </table>	Wire gauge		ø	Stripping length	1.5 mm ²	AWG 16	1.75 mm	9.5 mm	2.5 mm ²	AWG 14	2.25 mm	9.5 mm	4 mm ²	AWG 12	2.85 mm	9.5 mm	6 mm ²	AWG 10	3.5 mm	9.5 mm	10 mm ²	AWG 8	4.3 mm	15 mm				
Wire gauge		ø	Stripping length																													
1.5 mm ²	AWG 16	1.75 mm	9.5 mm																													
2.5 mm ²	AWG 14	2.25 mm	9.5 mm																													
4 mm ²	AWG 12	2.85 mm	9.5 mm																													
6 mm ²	AWG 10	3.5 mm	9.5 mm																													
10 mm ²	AWG 8	4.3 mm	15 mm																													
Han D® HMC, Crimp contact, Contact surface: HMC gold plated 	0.14 ... 0.37 0.5 0.75 1 1.5 2.5	09 15 200 6124 09 15 200 6123 09 15 200 6125 09 15 200 6122 09 15 200 6121 09 15 200 6126	09 15 200 6224 09 15 200 6223 09 15 200 6225 09 15 200 6222 09 15 200 6221 09 15 200 6226	 <table border="1"> <thead> <tr> <th>Conductor cross-section</th> <th></th> <th>ø</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>0.14-0.37 mm²</td> <td>AWG 26-22</td> <td>0.9 mm</td> <td>8 mm</td> </tr> <tr> <td>0.5 mm²</td> <td>AWG 20</td> <td>1.1 mm</td> <td>8 mm</td> </tr> <tr> <td>0.75 mm²</td> <td>AWG 18</td> <td>1.3 mm</td> <td>8 mm</td> </tr> <tr> <td>1 mm²</td> <td>AWG 18</td> <td>1.45 mm</td> <td>8 mm</td> </tr> <tr> <td>1.5 mm²</td> <td>AWG 16</td> <td>1.75 mm</td> <td>8 mm</td> </tr> <tr> <td>2.5 mm²</td> <td>AWG 14</td> <td>2.25 mm</td> <td>6 mm</td> </tr> </tbody> </table>	Conductor cross-section		ø	Stripping length	0.14-0.37 mm ²	AWG 26-22	0.9 mm	8 mm	0.5 mm ²	AWG 20	1.1 mm	8 mm	0.75 mm ²	AWG 18	1.3 mm	8 mm	1 mm ²	AWG 18	1.45 mm	8 mm	1.5 mm ²	AWG 16	1.75 mm	8 mm	2.5 mm ²	AWG 14	2.25 mm	6 mm
Conductor cross-section		ø	Stripping length																													
0.14-0.37 mm ²	AWG 26-22	0.9 mm	8 mm																													
0.5 mm ²	AWG 20	1.1 mm	8 mm																													
0.75 mm ²	AWG 18	1.3 mm	8 mm																													
1 mm ²	AWG 18	1.45 mm	8 mm																													
1.5 mm ²	AWG 16	1.75 mm	8 mm																													
2.5 mm ²	AWG 14	2.25 mm	6 mm																													
Han D®, Han DD®, Han® DDD, Coding pin  <p>Only for crimp termination With loss of one contact</p>			09 33 000 9915																													

Han HMC