

## PushPull V4 plug, RJ45, Cat.6, IDC



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 145 1561
Specification	PushPull V4 plug, RJ45, Cat.6, IDC
HARTING eCatalogue	<a href="https://b2b.harting.com/09451451561">https://b2b.harting.com/09451451561</a>

### Identification

Category	Connectors
Series	HARTING PushPull (V4)
Identification	RJ45
Element	Connector sets

### Version

Termination method	IDC termination
Locking type	PushPull
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8
Pack contents	incl. housing with RJ45 connector, shielding and cable gland

### Technical characteristics

Conductor cross-section	0.1 ... 0.32 mm <sup>2</sup> Stranded
	0.22 ... 0.32 mm <sup>2</sup> Solid
Conductor cross-section	AWG 27/7 ... AWG 22/7 Stranded
	AWG 24/1 ... AWG 22/1 Solid
Limiting temperature	-40 ... +70 °C
Tightening torque	1.3 ... 1.5 Nm
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65
	IP67
Cable diameter	4.5 ... 10 mm
Transmission characteristics	Cat. 6 Class E up to 250 MHz



Pushing Performance

## Technical characteristics

Data rate	10 Gbit/s
Vibration resistance	10-500 Hz, 5 g, 0.35 mm, 2h/axis 5.72 m/s <sup>2</sup> acc. to IEC 61373 Category 1 Class B
Shock resistance	25 g / 11 ms, 3 shocks / axis and direction 5 g / 30 ms, 5 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

## Material properties

Material (hood/housing)	Thermoplastic
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Specifications	IEC 61076-3-106 Variant 4 (V4) EN 45545-2 R26: HL1, HL2, HL3
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079

## Commercial data

Packaging size	10
Net weight	27 g
Country of origin	Romania
European customs tariff number	85366990
eCl@ss	27440101 Rectangular connectors (set)