


this crimp contact should be processed with:

locator 09 99 000 0638

hand crimping tool 09 99 000 0509



surface specification				
pl	Ni [µm]	NiP [µm] (P=10,5-13%)	ΣNi+NiP [µm]	Au [µm]
1	min. 1,5	min. 1,5	max. 5,5	min. 0,15

	All Dimensions in mm Original Size DIN A4	Scale	Free size tol.		Ref.
		10:1			Sub.
	All rights reserved Department EL PD	Created by	Inspected by	Standardisation	Date
		HASSE	FRIESENH		2021-08-30
HARTING D-32339 Espelkamp		Title			Doc-Key / ECM-Nr.
		M12-P-CON-1.5-AWG14/2.5 mm <sup>2</sup> -F			100845226/UGD/001/B 500000201785
		Type	Number	Rev.	Page
		TB	21011009940	B	1/1