

## Connectors for pcb applications – general information

The range of pcb connectors available at HARTING is summarised in the table under. For each of the basic connector versions, the available contact styles are documented with termination process, pitch, plating, rating for power contacts and impedance for coaxial contact etc..., as well as the accessory configuration.

**Pcb connectors are delivered fully loaded** thus providing a very good positioning of the contacts in their cavities for an easy and safe insertion of the pins in the pcb holes particularly crucial in the right angled versions.

Due to the numerous possibilities offered with the pcb connectors, suggested method is to contact your local HARTING representative to determine the part number to order; see customer request form on pages 05.88 and 05.89.

|                  | Straight   |  | Right angled   |  |
|------------------|--|--|--|--|
| Insulator body   | <ul><li>Standard</li><li>SMC: Solder Reflow Compatible</li></ul>   |  | <ul> <li>Standard</li> <li>SMC: Solder Reflow Compatible</li> </ul>  |  |
| Signal contacts  | Solder termination<br>• Pitch: 2.84 mm<br>• Plating: 0.76 μm Au over Ni<br>• Pcb thickness from 1.6 to 3.2 mm  |  | Solder termination<br>• Pitch: 2.54 mm<br>• Plating: 0.76 μm Au over Ni<br>• Pcb thickness from 1.6 to 3.2 mm  |  |
| Power contacts   | Solder termination<br>• Rating: 20, 30, 40 A<br>• Plating: 0.76 μm Au over Ni  |  | Solder termination<br>• Rating: 20, 30, 40 A<br>• Plating: 0.76 μm Au over Ni  |  |
|                  | Press-in termination<br>● Rating: 30 A<br>● Plating: 0.76 μm Au over Ni  |  |  |  |
| Coaxial contacts | <ul> <li>Solder termination</li> <li>50 or 75 Ω</li> <li>Plating: <ul> <li>1.3 μm Au over Ni inner conductor</li> <li>0.76 μm Au over Ni outer ring</li> </ul> </li> </ul> |  | <ul> <li>Solder termination</li> <li>50 or 75 Ω</li> <li>Plating: <ul> <li>1.3 μm Au over Ni inner conductor</li> <li>0.76 μm Au over Ni outer ring</li> </ul> </li> </ul> |  |
| Accessories      | Through hole   |  | Metal bracket with<br>board lock and<br>through hole   |  |
|                  | Nut:<br>M3 or UNC 4-40   |  | Metal bracket with<br>board lock and<br>clinch nut M3<br>or UNC 4-40   |  |
|                  | Spacer:<br>M3 or UNC 4-40  |  | Metal bracket<br>with board lock<br>and female screw<br>lock UNC 4-40  |  |
|                  | Spacer<br>(M3 or UNC 4-40)<br>with board lock  |  |  |  |
|                  | Spacer<br>+ board lock<br>+ female screw lock<br>M3 or UNC 4-40  |  |  |  |