



LC duplex IP20 adapter for device integration

Advantages

- Small form factor requires 50 % (compared to SC and ST)
- Compact, space-saving design
- High packing density
- A & B parts identification according TIA 568 standard
- Complement adapter for IP67 connector on device side

Technical characteristics

Degree of protection	IP20
Mating interface	LC duplex with two fibres
Temperature range	-40 °C ... +70 °C

Identification	Part number	Drawing	Dimensions in mm															
Device side																		
Adapter																		
Multimode GOF	09 57 400 0003 000																	
Singlemode GOF	09 57 400 0004 000																	
Connector LC duplex																		
Multimode GOF	09 57 400 0001 000		<table border="1"> <thead> <tr> <th></th> <th>min.</th> <th>max.</th> </tr> </thead> <tbody> <tr> <td>G</td> <td>26.60</td> <td>26.80</td> </tr> <tr> <td>H</td> <td>9.35</td> <td>9.45</td> </tr> <tr> <td>J</td> <td>12.80</td> <td>12.90</td> </tr> <tr> <td>K</td> <td>15.24</td> <td>15.34</td> </tr> </tbody> </table>		min.	max.	G	26.60	26.80	H	9.35	9.45	J	12.80	12.90	K	15.24	15.34
	min.			max.														
G	26.60	26.80																
H	9.35	9.45																
J	12.80	12.90																
K	15.24	15.34																
Singlemode GOF	09 57 400 0002 000																	