

Technical characteristics

Ethernet interface – M12

Number of ports	8x 10/100Base-T(X)
Cable types according to IEEE 802.3	Shielded Twisted Pair (STP) or Unshielded Twisted Pair (UTP), Category 5
Data rate	10 Mbit/s or 100 Mbit/s (M12 D-coding)
Maximum cable length	100 m (Twisted Pair, with cable Category 5 acc. to DIN EN 50 173-1)
Termination	M12 D-coding (female)
Diagnostics (LED)	<ul style="list-style-type: none"> • Status Link - Green • Data transfer (Act) - Green flashing • Data transfer rate (Speed) - 100 Mbit/s: Yellow 10 Mbit/s: Green • Error - Red
Topology	<ul style="list-style-type: none"> • Line • Ring • Star • mixed

Power supply

Input voltage	24 / 48 V DC (12 V ... 60 V DC) - redundant
for Ha-VIS mCon 4080-B3V only	72 / 110 V DC (50.4 V ... 137.5 V DC) - redundant
Termination	M12 A-coding, male, for redundant power supply
Diagnostics (LED)	Power supply - LED Green

Design features

Housing material	metal
Dimensions (W x H x D)	130 x 166 x 50 mm (without connectors)
Degree of protection acc. to DIN EN 60 529	IP40
Assembly	Wall mounting, flat assembly
Weight	approx. 0.85 kg

Environmental conditions

Stock temperature	-40 °C ... +85 °C
Relative humidity	10 % ... +95 % (non-condensing)