



Ethernet Switch
Ha-VIS mCon 4080-BPoE1V
 8-port Ethernet Switch for flat installation

Managed	IP30	PROFINET compatible <input checked="" type="checkbox"/>	EtherNet/IP compatible <input checked="" type="checkbox"/>
Number of ports, Copper / Termination	8x 10/100Base-T(X) / M12 D-coding (female)		
mode PoE			
Input voltage / Termination	48 V DC		
Permissible range (min./max.)	46 V ... 55 V DC		
Input current	max. 3.0 A at 48 V DC with PoE; load 350 mA each port		
mode Non-PoE			
Input voltage / Termination	24 / 48 V DC / M12 A-coding, male, for redundant power supply		
Permissible range (min./max.)	12 V ... 55 V DC		
Input current	approx. 350 mA (at 24 V DC)		
Housing material	metal, powder-coated		
Dimensions (W x H x D)	130 x 166 x 50 mm (without connectors)		
Weight	approx. 0.85 kg		
Working temperature	-40 °C ... +70 °C		
MTBF	296.000 h		
Management	fully managed via Web interface and SNMP Functions see pages 01.141 and 01.142		

Identification	Part number	Drawing	Dimensions in mm
Ha-VIS mCon 4080-BPoE1V Ethernet Switch with 8 ports M12 D-coding for wall mounting	20 77 208 4009		