

## Features

- Suitable for Han D<sup>®</sup> / DD<sup>®</sup> inserts
- Can be combined with standard crimp contacts in one connector if needed
- Iron and constantan contacts according to IEC 60584 type J
- According to EUROMAP 14, Part 1

## Technical characteristics

Contact resistance	≤1 mΩ
Material (contacts)	Iron, Constantan compliant
RoHS	

## Specifications and approvals





EN 60664-1  
IEC 61984

## Details

**Crimping tools** see chapter Han 90

### Remarks on the crimp technique

The wire gauges mentioned in the catalogue refer to geometric wire gauges of cables.

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)
		Male	Female	
Han D <sup>®</sup> , Crimp contact, Iron  Contact surface: Gold plated  	0.14 ... 0.37	09 15 000 6171	09 15 000 6271	 Stripping length 8 mm
Han D <sup>®</sup> , Crimp contact, Constantan  	0.14 ... 0.37	09 15 000 6161	09 15 000 6261	 Stripping length 8 mm