





650 A 4.000 V 18 kV 3

Han  
HC

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)																					
		Male	Female																						
Han® HC Modular, 650, Crimp termination  <p>Please order crimp contacts separately.</p>	70 ... 240	09 11 001 3012	09 11 001 3112	 <p>max. wire outer diameter 70...185 mm<sup>2</sup>: 27 mm max. wire outer diameter 240 mm<sup>2</sup>: 32 mm</p>																					
TC 650, Crimp contact, Contact surface: Silver plated 	50 70 95 120 150 185 240	09 11 000 6561 09 11 000 6161 09 11 000 6162 09 11 000 6163 09 11 000 6164 09 11 000 6165 09 11 000 6168	09 11 000 6261 09 11 000 6262 09 11 000 6263 09 11 000 6264 09 11 000 6265 09 11 000 6268	 <table border="1"> <thead> <tr> <th>Conductor cross-section</th> <th>ø</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>70 mm<sup>2</sup></td> <td>11.5</td> <td>42 mm</td> </tr> <tr> <td>90 mm<sup>2</sup></td> <td>13.5</td> <td>42 mm</td> </tr> <tr> <td>120 mm<sup>2</sup></td> <td>15.5</td> <td>42 mm</td> </tr> <tr> <td>150 mm<sup>2</sup></td> <td>17</td> <td>42 mm</td> </tr> <tr> <td>185 mm<sup>2</sup></td> <td>19</td> <td>42 mm</td> </tr> <tr> <td>240 mm<sup>2</sup></td> <td>21.5</td> <td>46 mm</td> </tr> </tbody> </table> <p>for stranded wire according to IEC 60 228 Class 5 Crimp zone acc. to DIN 46235</p>	Conductor cross-section	ø	Stripping length	70 mm <sup>2</sup>	11.5	42 mm	90 mm <sup>2</sup>	13.5	42 mm	120 mm <sup>2</sup>	15.5	42 mm	150 mm <sup>2</sup>	17	42 mm	185 mm <sup>2</sup>	19	42 mm	240 mm <sup>2</sup>	21.5	46 mm
Conductor cross-section	ø	Stripping length																							
70 mm <sup>2</sup>	11.5	42 mm																							
90 mm <sup>2</sup>	13.5	42 mm																							
120 mm <sup>2</sup>	15.5	42 mm																							
150 mm <sup>2</sup>	17	42 mm																							
185 mm <sup>2</sup>	19	42 mm																							
240 mm <sup>2</sup>	21.5	46 mm																							