



For detailed information see catalogue DIN 41612 or www.HARTING.com

Type	Maximum number of contacts	Image		Termination								
				Solder	Reflow Soldering (SMC)	Solder lug	Press-in	Crimp	Wire wrap	Faston	Cage clamp	
H	15		male	3.0 mm							X	
			female	2.7 mm 4.0 mm 5.5 mm 7.0 mm 10.0 mm			3.6 mm				X	X
H	16		male	3.0 mm								
			female								X	
H 3	3		male	3.0 mm								
			female	4.0 mm								
MH	24 + 7		male	3.0 mm							X	
			female	4.5 mm				X	22.0 mm			
MH	21 + 5		male	3.1 mm								
			female	3.2 mm								

DIN 41612

Technical characteristics DIN Power

Number of contacts	3 – 48	Insertion and withdrawal force	
Contact spacing	5.08 mm; 2.54 mm	Type D, E	32-pol. ≤ 40 N 48-pol. ≤ 75 N
Working current (all contacts are loaded)	Type D, E, F, F9, FM, 2F 6 A max. Type H, H 3 15 A max.	Type F, F9, FM, 2F	24-pol. ≤ 37 N 32-pol. ≤ 50 N 45-pol. ≤ 70 N 48-pol. ≤ 75 N
		Type H	≤ 90 N
		Type H 3	≤ 20 N
Test voltage $U_{r.m.s}$	Type D, E, F, F9, FM, 2F ≥ 1.55 KV Type H ≥ 3.1 KV Type H 3 ≥ 2.5 KV	Materials	
		Mouldings	thermoplastic resin, glass-fibre filled, UL 94-V0 Poly Cyclohexylene Terephthalate (PCT), UL 94-V0
		Contacts	NFF classification up to F1/I2 copper alloy
Contact resistance	≤ 15 mΩ Solder and Wire wrap connection ≤ 20 mΩ Crimp connection	Contact surface	
Insulation resistance	≥ 10 ¹² Ω	Contact zone	selectively plated according to performance level hard silver plated or gold plated
Temperature range	-40 °C ... +105 °C Press-in connector -55 °C ... +125 °C max. + 240 °C for 15 s during reflow soldering (only SMC)		