




Identification	Part No.	Drawing	Dimensions in mm
----------------	----------	---------	------------------


Fibre optic cable, double ended, multi mode, 62.5 µm overmolded

Length: a = 1 m	33 58 231 0010 016
a = 5 m	33 58 231 0050 016
a = 10 m	33 58 231 0100 016
a = 20 m	33 58 231 0200 016
a = 40 m	33 58 231 0400 016
a = 50 m	33 58 231 0500 016
a = 60 m	33 58 231 0600 016
a = 100 m	33 58 231 1000 016
a = 300 m	33 58 231 3000 016

double ended




a = length




Loading-Plan

A — blue — B  
B — orange — A



Fibre optic breakout cable, multi mode, 62.5 µm

Length: 10 m	33 58 751 0100 001
Length: 20 m	33 58 751 0200 001
Length: 100 m	33 58 751 1000 001



PUR jacket  
 2-fibre multi mode 62.5 µm  
 Outer diameter: 7 mm  
 Min. bending radius:  
 Installation: 10.5 cm  
 Operating: 7.0 cm