

Han® PushPull, type acc. to IEC 61 076-3-118  
Panel feed-through, 5-poles, 690 V, 16 A

Features

- HARTING PushPull technology
- Compact, space-saving design
- Touch-proof
- Panel feed-through: male
  - crimp termination
  - Han-Quick Lock® termination technology
- 4 times coding without contact loss
- NEW: Larger termination cross section for conductors 0.25 - 1.5 mm<sup>2</sup>

Technical characteristics

Locking	PushPull technology acc. to IEC 61 076-3-117 variant 14 acc. to IEC 61 076-3-118
Mating face	IP65 / IP67
Degree of protection	4 + PE
Number of contacts	16 A 690 V 4 kV 3
Electrical data	0.25 – 2.5 mm <sup>2</sup>
acc. to DIN EN 61 984	min. 500
Termination cross section	-40 °C ... +70 °C
Mating cycles	Plastic, black
Temperature range	V0
Housing material	
Flammability acc. to UL 94	


Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

Han® PushPull Power 4/0  
Panel feed-through

5-poles, 690 V / 16 A  
incl. bulkhead housing and male insert

with crimp termination  
(Order crimp male contacts separately)


09 35 231 0331



with Han-Quick Lock® termination

0.5 ... 2.5 mm<sup>2</sup>  
0.25 ... 1.5 mm<sup>2</sup>

09 35 232 0331  
09 35 234 0331



Coding element

10 pieces each for device and cable side  
enables 4 times coding without contact loss

09 35 000 6190