



Ethernet Switch

Ha-VIS mCon 9080-B1V

8-port Ethernet Switch for installation in a 19" rack

Managed	IP20	PROFINET compatible <input checked="" type="checkbox"/>	EtherNet/IP compatible <input checked="" type="checkbox"/>
Number of ports, Copper / Termination	8x 10/100Base-T(X) / M12 D-coding (female)		
Input voltage / Termination	24 / 48 V DC / DIN frame connector, Type F		
Permissible range (min./max.)	8 V ... 60 V DC		
Input current	approx. 130 mA (at 24 V DC)		
Alarm signalling contact	Change-over contact, potential-free, 24 V DC / 0.5 A DIN frame connector, Type F		
Housing material	aluminium, anodised		
Dimensions (W x H x D)	60.6 mm (3 U) x 128.4 mm (12 HP) x 173.5 mm		
Weight	approx. 0.6 kg		
Working temperature	-40 °C ... +70 °C		
MTBF	631.000 h		
Management	fully managed via Web interface and SNMP Functions see pages 01.141 and 01.142		

Identification	Part number	Drawing	Dimensions in mm
Ha-VIS mCon 9080-B1V Ethernet Switch with 8 ports M12 D-coding	20 76 208 7002		M12x1 11,8 173,5