



## Unmanaged Plug-and-Play Ethernet Switches

for Assembly on DIN Rail in Control Cabinets

Commercial Temp.: 0 °C ... +55 °C / Industrial Temp.: -40 °C ... +70 °C

## Specification

Number of ports copper / termination	6 x 10BASE-Te / 100BASE-TX EEE / RJ45 (twisted pair)
Number of ports F.O. / termination	2 x 100BASE-FX / SC duplex socket
Nominal voltage	24 / 48 VDC =
Permissible voltage range	9 V ... 60 VDC =
Termination	Screw type terminal block, pluggable, 3-poles (+ / - / ⚡)
Current consumption typical @ 24 V / 48 V	113 mA - 119 mA / 60 mA - 69 mA
Dimensions (W x H x D)	120 x 113.5 x 27.3 mm (without pluggable screw type terminal block)
Weight	380 g - 386 g
MTBF in million hours	1.20 - 1.23
Approvals	CE FCC CFR 47 Part 15, cUL US 508 listed, Det Norske Veritas (DNV), Germanischer Lloyd (GL), American Bureau of Shipping (ABS), Nippon Kaiji Kyokai (NK)

Identification	Part number	Drawing	Dimensions in mm
Ha-VIS eCon 2062B-AD 0 °C ... +55 °C 2 x MM (2 km)	24 02 006 2110		
Ha-VIS eCon 2062B-AF 0 °C ... +55 °C 2 x SM (15 km)	24 02 006 2210		
Ha-VIS eCon 2062BT-AD -40 °C ... +70 °C 2 x MM (2 km)	24 02 006 2100		
Ha-VIS eCon 2062BT-AF -40 °C ... +70 °C 2 x SM (15 km)	24 02 006 2200		