





350 A 2.000 V 12 kV 3

Han
HC

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)																					
		Male	Female																						
Han® HC Modular, 350, Crimp termination  Please order crimp contacts separately.	25 ... 120	09 11 001 3001	09 11 001 3101	 <p>M</p> <p>F</p> <p>max. wire outer diameter 22 mm</p>																					
TC 350, Crimp contact, Contact surface: Silver plated 	25 35 50 70 95 120	09 11 000 6139 09 11 000 6140 09 11 000 6141 09 11 000 6142 09 11 000 6143 09 11 000 6144	09 11 000 6239 09 11 000 6240 09 11 000 6241 09 11 000 6242 09 11 000 6243 09 11 000 6244	 <table border="1" data-bbox="997 1310 1444 1500"> <thead> <tr> <th>Conductor cross-section</th> <th>ø</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>25 mm²</td> <td>7</td> <td>26 mm</td> </tr> <tr> <td>35 mm²</td> <td>8.2</td> <td>26 mm</td> </tr> <tr> <td>50 mm²</td> <td>10</td> <td>28 mm</td> </tr> <tr> <td>70 mm²</td> <td>11.5</td> <td>28 mm</td> </tr> <tr> <td>95 mm²</td> <td>13.5</td> <td>30 mm</td> </tr> <tr> <td>120 mm²</td> <td>15.5</td> <td>24 mm</td> </tr> </tbody> </table> <p>for stranded wire according to IEC 60 228 Class 5</p> <p>for stranded wire according to IEC 60228 Class 5</p> <p>Crimp zone acc. to DIN 46235</p>	Conductor cross-section	ø	Stripping length	25 mm ²	7	26 mm	35 mm ²	8.2	26 mm	50 mm ²	10	28 mm	70 mm ²	11.5	28 mm	95 mm ²	13.5	30 mm	120 mm ²	15.5	24 mm
Conductor cross-section	ø	Stripping length																							
25 mm ²	7	26 mm																							
35 mm ²	8.2	26 mm																							
50 mm ²	10	28 mm																							
70 mm ²	11.5	28 mm																							
95 mm ²	13.5	30 mm																							
120 mm ²	15.5	24 mm																							