


Number of contacts

15



Female connectors

| Identification | No. of contacts | Part number | Drawing | Dimensions in mm |
|--|-----------------|--|---|------------------|
| <p>Female connector with cage clamp May be used in a shell housing</p> | <p>15</p> | <p>Performance level 1 acc. to IEC 60 603-2</p> <p>09 06 015 2813^{f)}</p> | <p>Contact arrangement View from termination side Slot for screw driver</p> <p>Shell housing see chapter 20</p> | |
| <p>Panel cut out</p> | | | | |
| <p>Termination instructions</p> | | | <p>Screw driver width: 2.5 x 0.4 mm Stripping length: 4 - 10 mm Wire gauge: 0.14 - 1.5 mm² (AWG 26 - 16)</p> | |

DIN Power up to 15 A

^{f)} Railway classification NFF 16-101, Smoke index: F1, Flammability class: I2