





# Overview Han® crimping tools



Crimp contacts Series	Part number				mm <sup>2</sup>	AWG	Crimping machines								
	male contact silver plated	female contact silver plated	male contact gold plated	female contact gold plated			09 99 000 0314	09 99 000 0307	09 98 000 6901 1)	09 98 000 6902 1)	09 98 000 6903 1)	09 98 000 6907 1)	09 98 000 9001	09 98 000 9002	09 98 000 9003
<b>Han D®</b> Signal contacts 09 15 000 .... 	6107	6207	6127	6227	0.14 - 0.25	26 - 24	x		x <sup>2)</sup>				x		
	6104	6204	6124	6224											
	6107	6207	6127	6227	0.37	22	x		x				x		
	6104	6204	6124	6224							x				x
	6103	6203	6123	6223	0.5	20	x		x				x		
	6105	6205	6125	6225	0.75	18	x		x				x		
	6102	6202	6122	6222	1.0	18	x		x				x		
	6101	6201	6121	6221	1.5	16	x		x				x		
6106	6206	6126	6226	2.5	14			x				x			
<b>Han E®</b> Power contacts 09 33 000 .... 	6127	6227	6117	6217	0.14 - 0.37	26 - 22	x			x <sup>2)</sup>					x
	6121	6220	6122	6222	0.5	20	x			x					x
	6114	6214	6115	6215	0.75	18	x			x					x
	6105	6205	6118	6218	1.0	18	x			x					x
	6104	6204	6116	6216	1.5	16	x			x					x
	6102	6202	6123	6223	2.5	14	x			x					x
	6106	6206			3.0	12	x			x					x
	6107	6207	6119	6221	4.0	12	x			x					x
<b>Han-Yellock®</b> Power contacts 11 05 000 .... 	6101	6201	6121	6221	0.14 - 0.37	26 - 22								x	
	6102	6202	6122	6222	0.5	20								x	
	6103	6203	6123	6223	0.75	18								x	
	6104	6204	6124	6224	1.0	18								x	
	6105	6205	6125	6225	1.5	16								x	
	6106	6206	6126	6226	2.5	14								x	
	6107	6207	6127	6227	3.0	12								x <sup>3)</sup>	
	6108	6208	6128	6228	4.0	12								x <sup>3)</sup>	
<b>Han® C</b> Power contacts 09 32 000 .... 	6104	6204			1.5	16	x	x				x			x
	6105	6205			2.5	14	x	x				x			x
	6107	6207			4.0	12	x	x				x			x
	6108	6208			6.0	10		x				x			x
	6109	6209			10.0	8		x							x

Tools

1) TK-M basic machine 09 98 000 6900 is required  
 2) depending on the wire  
 3) only with modification 09 98 503 6900