

Identification	for use with	Part number	Drawing	Dimensions in mm															
Removal tool for moulding	Male connectors Type Q, 2Q, 3Q R, 2R, 3R	09 99 000 0198		12															
Removal tool for single male contacts		09 99 000 0239																	
Insertion tool for single male press-in contacts		09 99 000 0200		50 40 11															
Press-out tool	Termination length 17 mm 13 - 13.2 mm 11.5 mm 4.5 - 5.3 mm	09 99 000 0197 09 99 000 0219 09 99 000 0221 09 99 000 0220		<table border="1"> <thead> <tr> <th>Termination length [mm]</th> <th>x [mm]</th> <th>y [mm]</th> </tr> </thead> <tbody> <tr> <td>17</td> <td>12</td> <td>18.7</td> </tr> <tr> <td>13 - 13.2</td> <td>12</td> <td>22.7</td> </tr> <tr> <td>11.5</td> <td>14</td> <td>20.1</td> </tr> <tr> <td>4.5 - 5.3</td> <td>12</td> <td>30.2</td> </tr> </tbody> </table> <p>With the different dimension y no adjustment of hand bench press necessary.</p>	Termination length [mm]	x [mm]	y [mm]	17	12	18.7	13 - 13.2	12	22.7	11.5	14	20.1	4.5 - 5.3	12	30.2
Termination length [mm]	x [mm]	y [mm]																	
17	12	18.7																	
13 - 13.2	12	22.7																	
11.5	14	20.1																	
4.5 - 5.3	12	30.2																	
Termination support for protection against bending of 13 mm - 17 mm terminations	Male connectors Type Q, 2Q, 3Q R, 2R, 3R Female connectors Type B, 2B, 3B C, 2C, 3C	09 99 000 0240		11 95 5,4															
	Female connectors Type F	09 99 000 0241		14,8 87,5 4,8															
Support block for repair and removal	Male connectors Type Q, 2Q, 3Q R, 2R, 3R SEK 18* Female connectors Type B, 2B, 3B C, 2C, 3C F	09 99 000 0218		40 100 26 40,7															

* Connectors see separate catalogue