Han® Gigabit module



Features

- · Shielding bus separate from housing potential
- Suitable for the transmission of sensitive signals (e.g. bus
- Usable for Gigabit Ethernet cat. 6A
- · Suitable for PoE++

Technical characteristics

Number of contacts

+ shielding Additional contacts Rated current 5 A Rated voltage 50 V Rated impulse voltage 0.8 kV

Pollution degree

50 V AC, 60 V DC Rated voltage

Rated voltage acc. to UL 30 V $>10^{10} \Omega$ Insulation resistance Contact resistance ≤10 mΩ Contact resistance, shielding ≤100 mΩ -40 ... +85 °C Limiting temperature

Mating cycles ≥500

Cat. 6_A , Class E_A up to 500 MHz, Cat. 7_A , Class F_A up to Transmission characteristics

1,000 MHz

Data rate 10 Mbit/s, 100 Mbit/s, 1 Gbit/s,

10 Gbit/s

Material (insert) Polycarbonate (PC) Material (shielding) Zinc die-cast, nickel-plated Colour (insert) RAL 7032 (pebble grey)

Material (contacts) Copper alloy

Material flammability class acc.

to UL 94

RoHS compliant, compliant with

exemption

Specifications and approvals

EN 60664-1 IEC 61984

UL 1977 ECBT2.E235076

CSA-C22.2 No. 182.3 ECBT8.E235076

DNV GL

Modular