



Technical characteristics

Contact resistance $\leq 1 \text{ m}\Omega$
 Material (contacts) Copper alloy

Specifications and approvals

EN 60664-1
 IEC 61984

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)																		
		Male	Female																			
Han® HsB, Crimp contact, Contact surface: Silver plated 	1.5	09 31 000 6104	09 31 000 6204	 <table border="1"> <thead> <tr> <th>Wire gauge</th> <th>Ø</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>1.5 mm² AWG 16</td> <td>1.78 mm</td> <td>9.5 mm</td> </tr> <tr> <td>2.5 mm² AWG 14</td> <td>2.28 mm</td> <td>9.5 mm</td> </tr> <tr> <td>4 mm² AWG 12</td> <td>2.88 mm</td> <td>9.5 mm</td> </tr> <tr> <td>6 mm² AWG 10</td> <td>3.53 mm</td> <td>9.5 mm</td> </tr> <tr> <td>10 mm² AWG 8</td> <td>4.33 mm</td> <td>9.5 mm</td> </tr> </tbody> </table>	Wire gauge	Ø	Stripping length	1.5 mm ² AWG 16	1.78 mm	9.5 mm	2.5 mm ² AWG 14	2.28 mm	9.5 mm	4 mm ² AWG 12	2.88 mm	9.5 mm	6 mm ² AWG 10	3.53 mm	9.5 mm	10 mm ² AWG 8	4.33 mm	9.5 mm
	Wire gauge	Ø	Stripping length																			
	1.5 mm ² AWG 16	1.78 mm	9.5 mm																			
	2.5 mm ² AWG 14	2.28 mm	9.5 mm																			
	4 mm ² AWG 12	2.88 mm	9.5 mm																			
6 mm ² AWG 10	3.53 mm	9.5 mm																				
10 mm ² AWG 8	4.33 mm	9.5 mm																				
2.5	09 31 000 6105	09 31 000 6205																				
4	09 31 000 6101	09 31 000 6201																				
6	09 31 000 6102	09 31 000 6202																				
10	09 31 000 6103	09 31 000 6203																				