


Number of contacts

max. 64



Female connectors

DIN Signal up to 2 A

Identification	No. of contacts	Part number	Drawing	Dimensions in mm
Female connector for crimp contacts Order contacts separately	64	09 02 064 3214 ¹⁾		
Shell housing 09 02 064 0501 / 09 02 064 0502 see chapter 20				

Identification	Part number	Performance levels according to IEC 60603-2. Explanation chapter 00	
		2	1
Female crimp contacts BC			
Bandoliered contacts (approx. 5,000 pieces)	09 02 000 6484		09 02 000 6474
Bandoliered contacts (approx. 500 pieces)	09 02 000 8434		09 02 000 8444
Individual contacts ¹⁾	09 02 000 8484		09 02 000 8474

Wire gauge mm ² AWG Insulation ø mm 0.09 - 0.5 28 - 20 0.7 - 1.5	
3.5 + 0.5 mm of insulation is stripped from the wires to be crimped For the fabrication in line with the specification please use exclusively crimp tools approved by HARTING (see DIN EN 60352-2) Insertion, removal and crimping tools see chapter 30	

¹⁾ Packaging unit 1,000 pieces
²⁾ Railway classification NFF 16-101, Smoke index: F1, Flammability class: I2