














Summary contact inserts Han® 3 A



Series	Han® Q 5/0	Han® Q 5/0 Quick Lock	Han® Q 5/0 Quick Lock	Han® Q 7/0
Number of contacts	5 + ⊕	5 + ⊕	5 + ⊕	7 + ⊕
Termination	Crimp terminal 	Quick Lock termination 	Quick Lock termination 	Crimp terminal 
Rated current	16 A	16 A	16 A	10 A
Rated voltage	230 / 400 V	230 / 400 V	230 / 400 V	400 V
Wire gauge	0.14 ... 2.5 mm ²	0.5 ... 2.5 mm ²	0.25 ... 1.5 mm ²	0.14 ... 2.5 mm ²
Male insert (M)	09 12 005 3001	09 12 005 2633	09 12 005 2634	09 12 007 3001
Female insert (F)	09 12 005 3101	09 12 005 2733	09 12 005 2734	09 12 007 3101

Series	Han® Q 12/0	Han® Q 12/0	Han® Q High Density	
Number of contacts	12 + ⊕	12 + ⊕	21	
Termination	Crimp terminal / Quick Lock termination 	Crimp terminal / Quick Lock termination 	Crimp terminal 	
Rated current	10 A	10 A	6.5 A	
Rated voltage	400 V	400 V	~ 50 V / – 120 V	
Wire gauge	0.5 ... 2.5 mm ²	0.25 ... 1.5 mm ²	0.09 ... 0.56 mm ²	
Male insert (M)	09 12 012 3001	09 12 012 3004	09 12 021 3001	
Female insert (F)	09 12 012 3101	09 12 012 3104	09 12 021 3101	

Series	Staf® 6	Staf® 6		
Number of contacts	6	6		
Termination	Solder terminal 	Screw terminal 		
Rated current	10 A	10 A		
Rated voltage	~ 25 V / – 60 V	~ 25 V / – 60 V		
Wire gauge	2.5 mm ²	1.5 mm ²		
Male insert (M)	09 70 006 2615	09 70 006 2616		
Female insert (F)	09 70 006 2812	09 70 006 2813		

Series	Han-Brid® Cu	Han-Brid® Cu	Han-Brid® Cu	Han-Brid® Cu
Number of contacts	4 / 2	4 / 2	4 / 2	4 / 2
Termination	Crimp terminal / IDC Insulation displacement terminal 	Crimp terminal / Crimp terminal 	Cage-clamp terminal / Cage-clamp terminal 	Crimp terminal / Crimp terminal 
Rated current	10 A	10 A	10 A	10 A
Rated voltage	50 V	50 V	50 V	50 V
Wire gauge	0.14 ... 2.5 mm ²	0.14 ... 2.5 mm ²	0.14 ... 2.5 mm ²	0.14 ... 2.5 mm ²
Male insert (M)	09 12 006 2611	09 12 006 3001	09 12 006 2695	09 12 006 2694
Female insert (F)	09 12 006 2701	09 12 006 3111	09 12 006 2795	09 12 006 2794