

Number of contacts

2



Identification	Part number		Drawing	Dimensions in mm
	Male insert (M)	Female insert (F)		
Crimp termination Order crimp contacts separately	09 14 002 3003	09 14 002 3103		<p>Contact arrangement view from termination side</p>

Identification	Wire gauge mm ²	Partnumber		Drawing	Dimensions in mm																							
		Male contact	Female contact																									
Crimp contacts power contact silver plated 	1.5 2.5 4.0 6.0 10	09 32 000 6104 09 32 000 6105 09 32 000 6107 09 32 000 6108 09 32 000 6109	09 32 000 6204 09 32 000 6205 09 32 000 6207 09 32 000 6208 09 32 000 6209		<table border="1"> <thead> <tr> <th>Wire gauge</th> <th>Ø</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>1.5 mm²</td> <td>AWG 16</td> <td>1.75</td> <td>9.5 mm</td> </tr> <tr> <td>2.5 mm²</td> <td>AWG 14</td> <td>2.25</td> <td>9.5 mm</td> </tr> <tr> <td>4.0 mm²</td> <td>AWG 12</td> <td>2.85</td> <td>9.5 mm</td> </tr> <tr> <td>6.0 mm²</td> <td>AWG 10</td> <td>3.50</td> <td>9.5 mm</td> </tr> <tr> <td>10 mm²</td> <td>AWG 8</td> <td>4.30</td> <td>15 mm</td> </tr> </tbody> </table> <p>Stripping length a = 15 mm for cables ≥ 5 mm Stripping length a = 18 mm for cables ≥ 6.4 mm</p>	Wire gauge	Ø	Stripping length	1.5 mm ²	AWG 16	1.75	9.5 mm	2.5 mm ²	AWG 14	2.25	9.5 mm	4.0 mm ²	AWG 12	2.85	9.5 mm	6.0 mm ²	AWG 10	3.50	9.5 mm	10 mm ²	AWG 8	4.30	15 mm
Wire gauge	Ø	Stripping length																										
1.5 mm ²	AWG 16	1.75	9.5 mm																									
2.5 mm ²	AWG 14	2.25	9.5 mm																									
4.0 mm ²	AWG 12	2.85	9.5 mm																									
6.0 mm ²	AWG 10	3.50	9.5 mm																									
10 mm ²	AWG 8	4.30	15 mm																									