



Accessories and cable assemblies

Identification	Part number	Drawing	Dimensions in mm																								
Bracket with four cavities	27 71 040 0001	<p>Board drillings Component side</p>																									
Gasket with four cavities	27 71 040 0002																										
Standard har-link® cable assembly Cable: 5 twisted pairs, AWG 28, shielded, PVC Wiring: 1:1 Length: L = 0.5 m L = 1.0 m L = 2.0 m	33 27 243 0500 001 33 27 243 1000 002 33 27 243 2000 003	<p>har-link male IDC connector</p>																									
High end har-link® cable assembly Cable: 5 twisted pairs, AWG 30, double shielded, PVC Wiring: 1:1 Length: L = 0.5 m L = 1.0 m L = 2.0 m	33 27 243 0500 006 33 27 243 1000 007 33 27 243 2000 008																										
Cable: 5 twisted pairs, AWG 30, double shielded, PVC Wiring: acc. to IEEE 1355 Length: L = 0.5 m L = 1.0 m L = 2.0 m	33 27 243 0500 015 33 27 243 1000 016 33 27 243 2000 017	IEEE 1355 wiring	<table border="1"> <thead> <tr> <th>Connector 1</th> <th>Connector 2</th> <th>Connector 1</th> <th>Connector 2</th> </tr> </thead> <tbody> <tr> <td>2-e</td> <td>1-a</td> <td>1-c</td> <td>1-c</td> </tr> <tr> <td>1-e</td> <td>2-a</td> <td>2-b</td> <td>1-d</td> </tr> <tr> <td>2-d</td> <td>1-b</td> <td>1-b</td> <td>2-d</td> </tr> <tr> <td>1-d</td> <td>2-b</td> <td>2-a</td> <td>1-e</td> </tr> <tr> <td>2-c</td> <td>2-c</td> <td>1-a</td> <td>2-e</td> </tr> </tbody> </table>	Connector 1	Connector 2	Connector 1	Connector 2	2-e	1-a	1-c	1-c	1-e	2-a	2-b	1-d	2-d	1-b	1-b	2-d	1-d	2-b	2-a	1-e	2-c	2-c	1-a	2-e
Connector 1	Connector 2	Connector 1	Connector 2																								
2-e	1-a	1-c	1-c																								
1-e	2-a	2-b	1-d																								
2-d	1-b	1-b	2-d																								
1-d	2-b	2-a	1-e																								
2-c	2-c	1-a	2-e																								