



Ha-VIS preLink® Patch cables

Advantages

- Pre-assembled system cable, fast, flexible and reliable in the application
- Simple in handling
- Robust in design
- Installation of Ha-VIS preLink® cables for industrial environment
- Connection cable for control or distributor cabinets or within controllers

Technical characteristics

Cable types	4 x 2 AWG 27/7, shielded, S/FTP Cat. 7
Sheath material	PUR
Wiring	TIA/EIA 568B, 1:1
Transmission performance	Category 6 / Class EA up to 500 MHz acc. to ISO/IEC 11 801:2002, EN 50 173-1
Transmission rate	up to 10 Gbit/s
Shielding	Copper braid, tinned
Operating temperature range	
fixed operation	-35 °C ... +70 °C
flexible operation	-5 °C ... +50 °C
Standard lengths	0.6 m / 1 m / 2 m / 3 m / 5 m / 10 m other lengths available on request
Colour	Yellow

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

Ha-VIS preLink® Patch cable

Yellow

terminal module to one side, secured by protection cap	Length	Part number
	0.2 m	20 82 600 1002
	0.4 m	20 82 600 1004
	0.6 m	20 82 600 1006
	0.8 m	20 82 600 1008
	1.0 m	20 82 600 1010
	2.0 m	20 82 600 1020
	3.0 m	20 82 600 1030
	4.0 m	20 82 600 1040
	5.0 m	20 82 600 1050
	10.0 m	20 82 600 1100



terminal module to both sides, secured by protection cap	Length	Part number
	0.2 m	20 82 600 2002
	0.4 m	20 82 600 2004
	0.6 m	20 82 600 2006
	0.8 m	20 82 600 2008
	1.0 m	20 82 600 2010
	2.0 m	20 82 600 2020
	3.0 m	20 82 600 2030
	4.0 m	20 82 600 2040
	5.0 m	20 82 600 2050
	10.0 m	20 82 600 2100



Side 1 with terminal module, secured by protection cap	Length	Part number
	0.2 m	20 82 601 1002
	0.4 m	20 82 601 1004
	0.6 m	20 82 601 1006
	0.8 m	20 82 601 1008
	1.0 m	20 82 601 1010
	2.0 m	20 82 601 1020
	3.0 m	20 82 601 1030
	4.0 m	20 82 601 1040
	5.0 m	20 82 601 1050
	10.0 m	20 82 601 1100



Side 2 RJ45 overmoulded, with locking lever protection

