# Han-Yellock® 60 hoods/housings



/ellock

## **Features**

- for six Han-Yellock® modules
- · High robustness due to internal locking mechanism
- · Two-part hood
- Earthed contacts PE in crimped or Han-Quick Lock® termination
- · Protection cover retrofit on housing side

#### Technical characteristics

Un-/locking temperature -10 ... +85 °C
Limiting temperature -40 ... +125 °C
Mating cycles ≥500
Degree of protection acc. to IEC IP65, IP67

60529

Material (hood/housing) Zinc die-cast, Aluminium die-

cast

Surface (hood/housing) Passivated, Powder-coated Colour (hood/housing) Metallic, RAL 7021 (black grey),

RAL 9005 (jet black)

Material (seal) NBI

Material (locking) Polyamide (PA), Stainless steel

Colour (locking) Melon yellow

Material flammability class acc.

to UL 94

RoHS compliant

## Specifications and approvals

EN 60664-1 IEC 61984 DNV GL



### **Details**





- ① M4 fixing screw (screw length > 20 mm, tightening torque: 1Nm)
- ② Panel fastener (tightening torque: 2.3 Nm)