

Number of contacts

# max. 48



## Accessories

Identification	No. of contacts	Part number	Drawing	Dimensions in mm																
<b>Female FC crimp contacts</b> individual contacts <sup>1)</sup> FC1 FC2 FC3 Bandoliered contacts (approx. 2,500 pcs.) FC1 FC2 FC3			<table border="1"> <thead> <tr> <th>Identi- fication</th> <th>Wire gauge mm<sup>2</sup></th> <th>AWG</th> <th>Insulations <math>\varnothing</math> mm</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>0.09-0.25</td> <td>28-24</td> <td>0.7-1.5</td> </tr> <tr> <td>2</td> <td>0.14-0.56</td> <td>26-20</td> <td>0.8-2.0</td> </tr> <tr> <td>3</td> <td>0.50-1.50</td> <td>20-16</td> <td>1.6-2.8</td> </tr> </tbody> </table> <p>3.5 + 0.5 mm of insulation is stripped from the wires to be crimped.                      For the fabrication in line with the specification please use exclusively crimp tools approved by HARTING (see DIN EN 60352-2)                      Crimping tools see chapter 30</p>	Identi- fication	Wire gauge mm <sup>2</sup>	AWG	Insulations $\varnothing$ mm	1	0.09-0.25	28-24	0.7-1.5	2	0.14-0.56	26-20	0.8-2.0	3	0.50-1.50	20-16	1.6-2.8	
Identi- fication	Wire gauge mm <sup>2</sup>	AWG	Insulations $\varnothing$ mm																	
1	0.09-0.25	28-24	0.7-1.5																	
2	0.14-0.56	26-20	0.8-2.0																	
3	0.50-1.50	20-16	1.6-2.8																	
<b>Mateable with 1 x 1 mm wrap posts</b>																				
<b>Distance fixing brackets for female connectors</b> Type D Type E		top (pos. 2) 09 04 000 9907 <sup>f)</sup>  bottom (pos. 32) 09 04 000 9906 <sup>f)</sup>																		
Type F I II		top (pos. 2) 09 06 000 9936 <sup>f)</sup>  bottom (pos. 32) 09 06 000 9937 <sup>f)</sup>																		

DIN Power up to 6 A

<sup>1)</sup> Packaging unit 1,000 pieces  
<sup>f)</sup> Railway classification NFF 16-101, Smoke index: F1, Flammability class: I2