



Han® PushPull Metal Outlet acc. to IEC 61 076-3-117 variant 14  
Cat. 6<sub>A</sub>, 8 poles

## Advantages

- Simple mounting, fixing and earth connection both outside
- Fast termination of data cables due to Ha-VIS preLink® technology
- Structured cabling for industrial premises
- Mating face AIDA compliant, protection cover incl.
- PROFINET compatible

## Technical characteristics

Number of ports, Copper/Termination	2 x Han® PushPull (V14) RJ45 (IP65 / IP67) or Han® 3 A RJ45
Transmission performance	Category 6, Class E <sub>A</sub> up to 500 MHz acc. to ISO/IEC 11801, EN 50 173-1
Data rate	10 Mbit/s, 100 Mbit/s, 1 Gbit/s, 2,5 Gbit/s, 5 Gbit/s, 10 Gbit/s
Termination	preLink®
Wire gauge	AWG 24 ... 22 (0.25 mm <sup>2</sup> ... 0.34 mm <sup>2</sup> ) solid and stranded
Strand diameter	Ø 1.3 mm ... 1.6 mm
Cable diameter	7.2 mm ... 8 mm
Shielding	Fully shielded 360° flexible shielding termination
Mounting	Wall mounting
Dimensions (H x W x D)	105 x 105 x 40.5 mm
Degree of protection	IP65 / IP67
Operating temperature range	-40 °C ... +70 °C
Housing material	Aluminium, die-cast
Colour	Black

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

preLink®  
Han® PushPull Metal Outlet

20 82 104 0101

consists of:

- 1x Housing including protection covers
- 2x preLink® Set RJ45 jack AWG 22/23
- 2x Cable gland with slotted seal
- 1x Assembly instruction

