



HARTING M12
system cable, 4-wire, straight, PushPull Press & Go

Features

- Connector types M12 D-coding PushPull
- Category Cat. 5
- Number of wires 4
- Wiring 1:1
- Sheath material Elastomer, electron beam cross-linked

Application

- For harsh industrial environments
- For installation in railway applications

Benefits

- Robust design
- Protection degree IP65 / IP67
- Fire protection acc. to EN 45545-1, -2 and -5
- M12 PushPull for a fast and vibration-free connection

Technical characteristics

- Connector types HARTING M12 D-coding PushPull
- Railway cords type 4 x AWG 22/7, stranded
- Sheath material Elastomer, electron beam cross-linked
- Wiring 4 pole, 1:1
- Transmission performance Class D up to 100 MHz acc. to ISO/IEC 11801, EN 50173-1
- Data rate 10 Mbit/s, 100 Mbit/s
- Shielding Fully shielded, 360° shielding contact
- Operating temperature range fix operation -40 °C ... +85 °C
- Colour Black

Identification

Part number

Drawing

Dimensions in mm

HARTING
M12 system cable, 4-wire
both sides assembled

Black

Length	1.0 m	21 33 232 3401 010
	1.5 m	21 33 232 3401 015
	2.0 m	21 33 232 3401 020
	3.0 m	21 33 232 3401 030
	5.0 m	21 33 232 3401 050
	10.0 m	21 33 232 3401 100

