



High current contacts

DIN Signal up to 2 A

Identification	Part number	Performance level 1	Drawing	Dimensions in mm																				
High current male contacts for male connectors¹⁾																								
I for straight crimp termination	10 A 20 A 40 A	09 03 000 6113 09 03 000 6114 09 03 000 6115		<table border="1"> <thead> <tr> <th></th> <th>ø A</th> <th>ø B</th> <th>wire gauge [mm²]</th> <th>AWG</th> </tr> </thead> <tbody> <tr> <td>10 A</td> <td>1.85</td> <td>2.55</td> <td>1.5</td> <td>16</td> </tr> <tr> <td>20 A</td> <td>2.85</td> <td>3.70</td> <td>4</td> <td>12</td> </tr> <tr> <td>40 A</td> <td>4.40</td> <td>5.60</td> <td>10</td> <td>8</td> </tr> </tbody> </table>		ø A	ø B	wire gauge [mm ²]	AWG	10 A	1.85	2.55	1.5	16	20 A	2.85	3.70	4	12	40 A	4.40	5.60	10	8
	ø A	ø B	wire gauge [mm ²]	AWG																				
10 A	1.85	2.55	1.5	16																				
20 A	2.85	3.70	4	12																				
40 A	4.40	5.60	10	8																				
II for straight solder termination	10 A 20 A 40 A	09 03 000 6101 09 03 000 6102 09 03 000 6103		<table border="1"> <thead> <tr> <th></th> <th>ø</th> </tr> </thead> <tbody> <tr> <td>10 A</td> <td>1.7</td> </tr> <tr> <td>20 A</td> <td>2.8</td> </tr> <tr> <td>40 A</td> <td>4.8</td> </tr> </tbody> </table>		ø	10 A	1.7	20 A	2.8	40 A	4.8												
	ø																							
10 A	1.7																							
20 A	2.8																							
40 A	4.8																							
Leading contact	40 A	09 03 000 6133																						
III for angled pcb termination	max. 40 A*	09 03 000 6104		<table border="1"> <thead> <tr> <th></th> <th>x</th> <th>y</th> </tr> </thead> <tbody> <tr> <td>... 6104</td> <td>17.7</td> <td>6.4</td> </tr> <tr> <td>... 6134</td> <td>18.4</td> <td>7.0</td> </tr> </tbody> </table>		x	y	... 6104	17.7	6.4	... 6134	18.4	7.0											
	x	y																						
... 6104	17.7	6.4																						
... 6134	18.4	7.0																						
Leading contact	max. 40 A*	09 03 000 6134																						
IV for straight pcb termination	max. 40 A* max. 40 A*	09 03 000 6110 09 03 000 6135																						
* depending on the pcb design																								
High current female contacts for female connectors¹⁾																								
V for straight crimp termination	10 A 20 A 40 A	09 03 000 6213 09 03 000 6214 09 03 000 6215		<table border="1"> <thead> <tr> <th></th> <th>ø A</th> <th>ø B</th> <th>wire gauge [mm²]</th> <th>AWG</th> </tr> </thead> <tbody> <tr> <td>10 A</td> <td>1.85</td> <td>2.55</td> <td>1.5</td> <td>16</td> </tr> <tr> <td>20 A</td> <td>2.80</td> <td>3.70</td> <td>4</td> <td>12</td> </tr> <tr> <td>40 A</td> <td>4.40</td> <td>5.60</td> <td>10</td> <td>8</td> </tr> </tbody> </table>		ø A	ø B	wire gauge [mm ²]	AWG	10 A	1.85	2.55	1.5	16	20 A	2.80	3.70	4	12	40 A	4.40	5.60	10	8
	ø A	ø B	wire gauge [mm ²]	AWG																				
10 A	1.85	2.55	1.5	16																				
20 A	2.80	3.70	4	12																				
40 A	4.40	5.60	10	8																				
VI for straight solder termination	10 A 20 A 40 A	09 03 000 6201 09 03 000 6202 09 03 000 6203		<table border="1"> <thead> <tr> <th></th> <th>ø</th> </tr> </thead> <tbody> <tr> <td>10 A</td> <td>1.7</td> </tr> <tr> <td>20 A</td> <td>2.8</td> </tr> <tr> <td>40 A</td> <td>4.8</td> </tr> </tbody> </table>		ø	10 A	1.7	20 A	2.8	40 A	4.8												
	ø																							
10 A	1.7																							
20 A	2.8																							
40 A	4.8																							
VII for screw fixing on busbar	40 A	09 03 000 6245																						
for type M invers for solder termination	40 A	09 03 000 6207																						
VIII for type M-flat for press-in termination	40 A	09 03 000 6250																						
for solder termination	40 A	09 03 000 6225																						

¹⁾ Contact resistance max. 1.5 mΩ
²⁾ Contact resistance internal wire max. 3 mΩ