



Part-Number 09 99 000 0851

Features

- Closed hydraulic jack, hinged and rotatable
- Low weight due to premium aluminium housing
- 2-step hydraulic with fast forward motion and power stroke
- Automatic flyback after crimping

Technical characteristics

- Crimping force: 60 kN
- Crimp wire gauge range: 6 – 70 mm²
- Idle stroke: 17 mm
- Length: 460 mm
- Weight: 3.3 kg
- Ambient temperature: -20 °C ... +40 °C

Included with the set

- The tool comes in a metal case
- HARTING Hand-Hydraulic Crimp Tool 60 kN
- Metal case accommodates up to 17 HARTING crimp dies for 60 kN-tools

Suitable for

- Compatible with all HARTING crimp dies for 60 kN tools as well as with the respective contacts
 - TC 70
 - TC 100
 - TC 200
 - TC 250
 - TC 350 up to 70 mm²
 - TC 650 up to 70 mm²