



Features

- Compatible with all HARTING 60 kN crimp tools
- Optimal crimp process due to 9 mm wide crimp dies
- Polished crimp profile in order to achieve optimal termination results

Technical characteristics

- Crimp zone following DIN 46 235

Identification

Part-Number

Compatible contacts

		Compatible contacts	
		male	female
Crimp die 10 mm ² for 60 kN tools	09 99 000 0852	09 11 000 6131 09 11 000 6114	09 11 000 6231 09 11 000 6214
Crimp die 16 mm ² for 60 kN tools	09 99 000 0853	09 11 000 6132 09 11 000 6116	09 11 000 6232 09 11 000 6216
Crimp die 25 mm ² for 60 kN tools	09 99 000 0854	09 11 000 6120 09 11 000 6125 09 11 000 6126 09 11 000 6133 09 11 000 6139	09 11 000 6220 09 11 000 6225 09 11 000 6226 09 11 000 6233 09 11 000 6239
Crimp die 35 mm ² for 60 kN tools	09 99 000 0855	09 11 000 6104 09 11 000 6121 09 11 000 6127 09 11 000 6135 09 11 000 6140	09 11 000 6204 09 11 000 6221 09 11 000 6227 09 11 000 6235 09 11 000 6240
Crimp die 50 mm ² for 60 kN tools	09 99 000 0856	09 11 000 6122 09 11 000 6128 09 11 000 6141	09 11 000 6222 09 11 000 6228 09 11 000 6241
Crimp die 70 mm ² for 60 kN tools	09 99 000 0857	09 11 000 6123 09 11 000 6129 09 11 000 6142 09 11 000 6161	09 11 000 6223 09 11 000 6229 09 11 000 6242 09 11 000 6261