



**Part-Number 09 99 000 0900**

## Features

- High-capacity rechargeable battery punch driver
- Rotatable hydraulic cylinder and lithium-ion battery
- Fatigue-free punching due to easy handling and low weight
- Electronic monitoring of the punching process
- Compatible to all HARTING punch units

## Included with the set

- Tool comes in a plastic case
- HARTING Battery-Hydraulic Punch Driver
- Lithium-ion battery 18 V, 3 Ah
- Battery charger
- Draw stud 9.5 x 19.0 mm (3/8" x 3/4") UNF
- Draw stud 19.0 x 125.0 mm (3/4" x 5") UNF
- Spacer
- Lubricant
- HSS-E pilot drill (multi-step drill)
- 1 punch unit in size M16, M20, M25, M32 and Pg 16 each

## Technical characteristics

- Weight: 2 kg
- Punching capacity: 60 kN
- Battery voltage: 18 V DC
- Battery capacity: 3 Ah
- Battery charging time: 22 min
- Max. sheet thickness: 2 mm mild steel (acc. to EN 10 025)<sup>1)</sup>

<sup>1)</sup> Punch units for stainless steel available on request

## Suitable for

- HARTING punch units for hydraulic punch drivers