



High current contacts

Identification	Part number	Performance level 1	Drawing	Dimensions in mm																									
High current male contacts for male connectors¹⁾																													
I for straight crimp termination <table border="0" style="margin-left: 20px;"> <tr><td>10 A</td><td>09 03 000 6113</td></tr> <tr><td>20 A</td><td>09 03 000 6114</td></tr> <tr><td>40 A</td><td>09 03 000 6115</td></tr> </table>	10 A	09 03 000 6113	20 A	09 03 000 6114	40 A	09 03 000 6115	acc. to DIN 41626		<table border="1"> <thead> <tr> <th></th> <th>ø A</th> <th>ø B</th> <th>wire gauge [mm²]</th> <th>AWG</th> </tr> </thead> <tbody> <tr> <td>10 A</td> <td>1.85</td> <td>2.55</td> <td>1.5</td> <td>16</td> </tr> <tr> <td>20 A</td> <td>2.85</td> <td>3.70</td> <td>4</td> <td>12</td> </tr> <tr> <td>40 A</td> <td>4.40</td> <td>5.60</td> <td>10</td> <td>8</td> </tr> </tbody> </table>		ø A	ø B	wire gauge [mm ²]	AWG	10 A	1.85	2.55	1.5	16	20 A	2.85	3.70	4	12	40 A	4.40	5.60	10	8
	10 A	09 03 000 6113																											
	20 A	09 03 000 6114																											
	40 A	09 03 000 6115																											
	ø A	ø B	wire gauge [mm ²]	AWG																									
10 A	1.85	2.55	1.5	16																									
20 A	2.85	3.70	4	12																									
40 A	4.40	5.60	10	8																									
II for straight solder termination <table border="0" style="margin-left: 20px;"> <tr><td>10 A</td><td>09 03 000 6101</td></tr> <tr><td>20 A</td><td>09 03 000 6102</td></tr> <tr><td>40 A</td><td>09 03 000 6103</td></tr> </table> Leading contact <table border="0" style="margin-left: 20px;"> <tr><td>10 A</td><td>09 03 000 6111</td></tr> <tr><td>20 A</td><td>09 03 000 6122</td></tr> <tr><td>40 A</td><td>09 03 000 6133</td></tr> </table>	10 A	09 03 000 6101	20 A	09 03 000 6102	40 A	09 03 000 6103	10 A	09 03 000 6111	20 A	09 03 000 6122	40 A	09 03 000 6133	acc. to DIN 41626		<table border="1"> <thead> <tr> <th></th> <th>ø</th> </tr> </thead> <tbody> <tr> <td>10 A</td> <td>1.7</td> </tr> <tr> <td>20 A</td> <td>2.8</td> </tr> <tr> <td>40 A</td> <td>4.8</td> </tr> </tbody> </table>		ø	10 A	1.7	20 A	2.8	40 A	4.8						
	10 A	09 03 000 6101																											
	20 A	09 03 000 6102																											
	40 A	09 03 000 6103																											
10 A	09 03 000 6111																												
20 A	09 03 000 6122																												
40 A	09 03 000 6133																												
	ø																												
10 A	1.7																												
20 A	2.8																												
40 A	4.8																												
III for angled pcb termination <table border="0" style="margin-left: 20px;"> <tr><td>max. 40 A*</td><td>09 03 000 6110</td></tr> </table>	max. 40 A*	09 03 000 6110	acc. to DIN 41626		<table border="1"> <thead> <tr> <th></th> <th>x</th> <th>y</th> </tr> </thead> <tbody> <tr> <td>... 6104</td> <td>17.7</td> <td>6.4</td> </tr> <tr> <td>... 6134</td> <td>18.4</td> <td>7.0</td> </tr> </tbody> </table>		x	y	... 6104	17.7	6.4	... 6134	18.4	7.0															
	max. 40 A*	09 03 000 6110																											
	x	y																											
... 6104	17.7	6.4																											
... 6134	18.4	7.0																											
IV <table border="0" style="margin-left: 20px;"> <tr><td>max. 40 A*</td><td>09 03 000 6104</td></tr> <tr><td>Leading contact max. 40 A*</td><td>09 03 000 6134</td></tr> </table> * depending on the pcb design	max. 40 A*	09 03 000 6104	Leading contact max. 40 A*	09 03 000 6134	acc. to DIN 41626		<table border="1"> <thead> <tr> <th></th> <th>x</th> <th>y</th> </tr> </thead> <tbody> <tr> <td>... 6104</td> <td>17.7</td> <td>6.4</td> </tr> <tr> <td>... 6134</td> <td>18.4</td> <td>7.0</td> </tr> </tbody> </table>		x	y	... 6104	17.7	6.4	... 6134	18.4	7.0													
max. 40 A*	09 03 000 6104																												
Leading contact max. 40 A*	09 03 000 6134																												
	x	y																											
... 6104	17.7	6.4																											
... 6134	18.4	7.0																											
High current female contacts for female connectors¹⁾ for type M-flat																													
V for press-in termination <table border="0" style="margin-left: 20px;"> <tr><td>40 A</td><td>09 03 000 6250</td></tr> <tr><td>for solder termination 40 A</td><td>09 03 000 6225</td></tr> </table>	40 A	09 03 000 6250	for solder termination 40 A	09 03 000 6225	acc. to DIN 41626																								
40 A	09 03 000 6250																												
for solder termination 40 A	09 03 000 6225																												
Crimping tool for high current contacts		09 99 000 0196																											
Removal tool		09 99 000 0174																											
Replacement removal jacket																													
Removal tool		09 99 000 0328																											
Replacement removal jacket																													

¹⁾ Contact resistance max. 1.5 mΩ