



Features

- Integrated centre punch for exact positioning of mounting holes
- Long lifetime due to CAD-optimised punch geometry and special inert gas hardening
- Reduced punching forces due to innovative punch geometry
- Reduced punching force results in lower stress on hydraulic seals
- For use in combination with Hydraulic Punch Drivers 09 99 000 0900 and 09 99 000 0901

Technical characteristics

Max. sheet thickness 2 mm unalloyed steel¹⁾
 (acc. to EN 10025)

¹⁾ Punch units for stainless steel available on request

Identification

Part number

Han-Eco® 10 A Punch Unit
 Han-Eco® 16 A Punch Unit

09 99 000 0914
 09 99 000 0915

Panel cut out

32.1 x 62.6 mm
 32.1 x 79.1 mm