


Number of contacts

# 2



Identification	Wire gauge (mm <sup>2</sup> )	Part number		Drawing	Dimensions in mm												
		male	female														
<p>Han-Modular®, Han-Quintax® module</p> <p>Crimp terminal</p>		09 14 002 3001	09 14 002 3101	<p>M</p> <p>F</p> <p>Contact arrangement (view from termination side)</p>													
<p>Han-Modular®, Han-Quintax® High Density contact</p> <p>8 + shielding, for Han® D-Sub contacts</p> <p>Please order contacts separately</p>		09 15 008 3013	09 15 008 3113	<p>M</p> <p>F</p>													
<p>Han-Quintax® Adapter</p> <p>optional</p>		09 14 000 9915	09 14 000 9915														
<p>Han® D-Sub crimp contact, turned contacts</p>	<p>0.09-0.25</p> <p>0.13-0.33</p> <p>0.25-0.52</p>	<p>09 67 000 7576</p> <p>09 67 000 5576</p> <p>09 67 000 8576</p>	<p>09 67 000 7476</p> <p>09 67 000 5476</p> <p>09 67 000 8476</p>	<table border="1"> <thead> <tr> <th>Wire gauge</th> <th>max. Insulation Ø</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>0.09-0.25 mm<sup>2</sup></td> <td>1.7 mm</td> <td>4 mm</td> </tr> <tr> <td>0.13-0.33 mm<sup>2</sup></td> <td>1.7 mm</td> <td>4 mm</td> </tr> <tr> <td>0.25-0.52 mm<sup>2</sup></td> <td>1.7 mm</td> <td>4 mm</td> </tr> </tbody> </table>	Wire gauge	max. Insulation Ø	Stripping length	0.09-0.25 mm <sup>2</sup>	1.7 mm	4 mm	0.13-0.33 mm <sup>2</sup>	1.7 mm	4 mm	0.25-0.52 mm <sup>2</sup>	1.7 mm	4 mm	
Wire gauge	max. Insulation Ø	Stripping length															
0.09-0.25 mm <sup>2</sup>	1.7 mm	4 mm															
0.13-0.33 mm <sup>2</sup>	1.7 mm	4 mm															
0.25-0.52 mm <sup>2</sup>	1.7 mm	4 mm															