



Industrial Cat. 5e stranded cable, 8-wire, PVC, Outdoor

Features

- Sheath material PVC
- Category 5e
- Number of wires 8
- Wire design AWG 26/7
- Wire diameter (6.5 ... 6.9) mm

Application

- To build-up flexible connections (one- or two-sided assembled system cable)

Benefits

- Robust design suitable for industry
- Applicable also for outside applications
- UL, AWM style 2969
- Flame retardant
- Weather proof
- UV resistant
- RoHS compliant
- With Fast Connect inside sheath

Technical characteristics

Cable structure	4 x 2, Twisted Pair, shielded
Core structure	4 x 2 x AWG 26/7
Wire insulation	PE, Ø 1.0 mm
Sheath material	PVC
Cable sheath diameter	6.5 mm ... 6.9 mm
Transmission performance	Category 5e / Class D up to 100 MHz acc. to ISO/IEC 11801:2002, EN 50 173-1
Transmission rate	10/100/1000 Mbit/s
Shielding	Foil screen and additional plaited cable
Operating temperature range	-10 °C ... +60 °C
Colour	Black

Identification

Industrial Cat. 5e stranded cable, 8-wire, outdoor
PVC

- 20 m ring
- 50 m ring
- 100 m ring
- 500 m drum

Part number

- 09 45 600 0230
- 09 45 600 0240
- 09 45 600 0200
- 09 45 600 0220

Drawing



Dimensions in mm