



HARTING PushPull acc. to IEC 61 076-3-106 variant 4
RJ45 panel feed-throughs

Advantages

- Small, space-saving PushPull Interfaces in IP65 / IP67
- Easy handling of RJ45 patch cords in switch cabinets or sets
- Mounting to casings

Technical characteristics

| | |
|------------------------------|---|
| Locking | PushPull Technology acc. to IEC 61 076-3-106 variant 4 |
| Data rate Cat. 5 versions | 10 Mbit/s, 100 Mbit/s, 1000 Mbit/s |
| Data rate Cat. 6 versions | 10 Mbit/s, 100 Mbit/s 1 Gbit/s, 10 Gbit/s |
| Shielding | fully shielded, 360° shielding contact |
| Mating cycles | min. 750 |
| Degree of protection | IP65 / IP67 |
| Temperature range | -40 °C ... +70 °C |
| Housing material | Plastic, black Zinc die-cast, shining |
| Flammability acc. to UL 94 | V0 |
| | UL approval (E102079) |

Connecting hardware

| Identification | Part number | Drawing | Dimensions in mm |
|---|----------------|---------|------------------|
| <p>Panel feed-through set category of transmission Cat. 5</p> <p>incl. housing bulkhead mounting EasyInstall metal with integrated seal, 2 x RJ45-jack board drillings for M3</p> | 09 45 295 1130 | | |
| <p>Panel feed-through set category of transmission Cat. 6</p> <p>incl. housing bulkhead mounting Compact, with integrated seal, 2 x RJ45-jack</p> | 09 45 245 1561 | | |